
PVC and HDPE Water & Pressure Pipe



HDPE Pipe

Potable Water Pipe

- · Diameter range of 34" 26" offered
- · IPS, CTS and DIPS pipe sizes
- · Certified to NSF 61 and FM
- Conforms to AWWA C901, AWWA C906, ASTM D 2737, ASTM D 3035 and ASTM F 714
- · Available in sticks, coils and reels
- Standard colors are black, black with blue striping and solid blue for tubing

TO A SOUND TO MATERIAL TO SOUND TO NOT SOUND

Wastewater Pipe

- · Diameter range of ¾" 26" offered
- · IPS, CTS and DIPS pipe sizes
- Conforms to AWWA C901, AWWA C906, ASTM D 2737, ASTM D 3035 and ASTM F 714
- · Available in sticks, coils and reels
- Standard colors are gray, black with green striping and solid green for tubing



Reclaimed Pipe

- · Diameter range of ¾" 26" offered
- IPS, CTS and DIPS pipe sizes
- Conforms to AWWA C901, AWWA C906, ASTM D 2737, ASTM D 3035 and ASTM F 714
- · Available in sticks, coils and reels
- Standard colors are black with lavender striping and solid lavender for tubing



Geothermal Pipe

- · Diameter range of 34" 26" offered
- · IPS pipe size
- · Conforms to ASTM D 3035 and ASTM F 714
- · Available in sticks, coils and reels
- · Standard color is black



Mining Pipe

- · Diameter range of 1" 26" offered
- · IPS pipe size
- · Conforms to ASTM D 3035 and ASTM F 714
- · Available in sticks, coils and reels
- Standard color is black with color striping available




HDPE Natural Gas Pipe

- · Diameter range of ½" 12" offered
- · IPS and CTS pipe sizes
- · Conforms to ASTM D 2513
- · Available in sticks, coils and reels
- · Standard color is black with yellow striping



Oil & Gas Pipe

- · Diameter range of ¾" 26" offered
- · IPS pipe size
- · Conforms to ASTM F 2619
- · Available in sticks, coils and reels
- · Standard color is black with color striping available



Fire Protection Pipe

- · Diameter range of 4" 26" offered
- · IPS and DIPS pipe sizes
- · Certified to FM
- · Conforms to AWWA C906 and ASTM F 714
- · Available in sticks, coils and reels
- · Standard color is black with red striping





Visit **atkore.com** for the latest product updates.

PVC Pipe

PVC AWWA C900 Pressure Pipe

- Conforms to AWWA C900 and UL1285 as listed by NSF in accordance with Standard NSF/ANSI 14
- · Listed to FM 1612 for DR 14 and DR 18 products
- Each spigot end is beveled to facilitate assembly and double reference marked to indicate proper insertion depth
- Product manufactured with one integral gasketed bell per length
- · Standard laying length of pipe is 20 feet
- · Standard color is blue
- · Green and purple are available upon request



PVC Schedule 40 Pressure Pipe

- Conforms to ASTM D 1785 and certified to the requirements of NSF/ANSI 61
- Conforms to ASTM D 2665 and is certified to requirements of NSF/ANSI 14 for DWV applications in 1½", 2", 3", 4", 6" and 8" trade sizes
- Product manufactured with one integral solvent-weld bell per length
- · Standard overall pipe length is 20 feet
- · Standard color is white



PVC Schedule 80 Pressure Pipe

- · Conforms to ASTM D 1785
- · Certified to the requirements of NSF/ANSI 61
- · Product manufactured in plain end
- · Standard overall pipe length is 20 feet
- · Standard color is gray



PVC IPS Solvent-Weld Pressure Pipe

- · Conforms to ASTM D 2241
- · Certified to the requirements of NSF/ANSI 61
- Product manufactured with one integral solvent-weld bell per length
- · Standard overall pipe length is 20 feet
- · Standard color is white



PVC IPS Gasketed Pressure Pipe

- · Conforms to ASTM D 2241
- · Certified to requirements of NSF/ANSI 61
- Each spigot end is beveled to facilitate assembly and reference marked to indicate proper insertion depth
- Product manufactured with one integral gasketed bell per length
- · Standard laying length of pipe is 20 feet
- · Standard color is white



PVC PIP Gasketed Pressure Pipe

- · Conforms to ASTM D 2241
- Each spigot end is beveled to facilitate assembly and reference marked to indicate proper insertion depth
- Products manufactured with one integral gasketed bell per length
- · Standard laying length of pipe is 20 feet
- · Standard color is white



PVC Gasketed Sewer Pipe

- · Conforms to ASTM D 3034 and ASTM F 679
- Each spigot end is beveled to facilitate assembly and reference marked to indicate proper insertion depth
- Products manufactured with one integral gasketed bell per length
- · Standard laying length of pipe is 14 or 20 feet
- · Standard color is green



PVC Solvent-Weld Sewer Pipe

- · Conforms to ASTM D 3034 DR 35 prior to perforation
- Product manufactured with one integral solvent-weld bell per length
- · Standard overall pipe length is 10 feet or 20 feet
- · Standard colors are white and green



PVC Drainage Pipe

- · Conforms to ASTM D 2729
- Product manufactured with one integral solvent-weld bell per length
- · Standard overall pipe length is 10 feet
- · Standard color is white



PVC Natural Gas Sleeving

- Product manufactured with one integral solvent-weld bell per length
- Pipe is intended for sleeving applications and carries no pressure rating
- · Standard overall pipe length is 20 feet
- · Standard color is yellow





Visit **atkore.com** for the latest product updates.

PVC Diameter Ranges by Region

Product	Eastern Region	Western Region
DWV Schedule 40 Cellular Core	1 ½" - 6"	1 ½" - 6"
DWV ASTM D 2949	3 1/4"	_
PR 165 DR 25 AWWA C900 GB	4" - 12"	4" - 12"
PR 235 DR 18 AWWA C900 GB	4" - 12"	4" - 12"
PR 305 DR 14 AWWA C900 GB	4" - 12"	4" - 12"
Schedule 40 Pressure	1⁄2" - 12"	1/2" - 8"
Schedule 80 Pressure	1/2" - 8"	1/2" - 8"
Schedule 40 F480 Well Casing	2" - 6"	_
PR 63 SDR 64 Gasketed	_	8"
PR 100 SDR 41 Gasketed	-	4" - 12"
PR 125 SDR 32.5 Gasketed	-	4" - 12"
PR 160 SDR 26 Gasketed	3" - 8"	4" - 12"
PR 200 SDR 21 Gasketed	1 1/2" - 8"	4" - 12"
PR 315 SDR 13.5 Gasketed	2"	-
PR 63 SDR 64 Solvent-Weld	_	8"
PR 100 SDR 41 Solvent-weld	3" - 6"	3" - 8"
PR 125 SDR 32.5 Solvent-weld	2 1/2" - 6"	1 1/4" - 8"
PR 160 SDR 26 Solvent-weld	1 1/4" - 6"	1 1/4" - 8"
PR 200 SDR 21 Solvent-weld	³/4" - 6"	3/4" - 8"
PR 315 SDR 13.5 Solvent-weld	1/2"	1/2"
ASTM D 3034 SDR 35 Gasketed Sewer	4" - 15"	4" - 15"
ASTM D 3034 SDR 26 Gasketed Sewer	4" - 15"	4" - 15"
ASTM F 679 PS 46 Gasketed Sewer	_	18"
ASTM F 679 PS 115 Gasketed Sewer	-	18"
ASTM D 3034 DR 35 Solvent-weld Sewer	4" - 8"	4" & 6"
PR 80 SDR 51 GB PIP	-	6" - 18"
PR 100 SDR 41 GB PIP	_	6" - 18"
PR 125 SDR 32.5 GB PIP	-	6" - 18"
ASTM D 2729 Drainage	3" - 6"	4" & 6"
Yellow Gas Sleeve	-	1 ½" - 8"



Learn more at **atkore.com**