


UNISTRUT® CONDUIT TRAPEZE SUPPORT



Atkore's New Conduit Trapeze Support offers labor and material savings.

Let Atkore aid in providing you a new way of mounting conduit, raceways and other needed accessories in one system. The Unistrut Conduit Trapeze Support comes in a variety of sizes ranging from 12" through 72", accommodating conduit up to 4 inches in width without needing additional components to tie down the conduit.

Key Features

- Conduit holes align conduits across trapeze
- Fewer components when compared to strut trapeze
- Eliminates need for conduit clamps at every support location
- No washers required at hanger locations
- No special tools required
- Flange accommodates ¼", ⅜", ½" threaded rod or bolts
- Can be mounted directly to decking or other structures
- Conduit clamps can be added to flange for additional rigidity
- Various products can be installed on the Support
- No cutting required
- Made in the USA

Product Options

- Lengths Available: 12", 24", 36", 48", 60", and 72"
- Accommodates up to 1 ¼", up to 2" and up to 4" Conduit
- Available in pregalvanized steel finish



Configurations



Conduit Trapeze Support - Up to 1 1/4" Conduit

Part Number	Description	Nominal Length	A	Conduit Hole
		in	in	
UCTS1-12PG	Conduit Trapeze Support, 1 1/4" conduit, PG	12	14	6
UCTS1-24PG	Conduit Trapeze Support, 1 1/4" conduit, PG	24	26	12
UCTS1-36PG	Conduit Trapeze Support, 1 1/4" conduit, PG	36	38	18
UCTS1-48PG	Conduit Trapeze Support, 1 1/4" conduit, PG	48	50	24
UCTS1-60PG	Conduit Trapeze Support, 1 1/4" conduit, PG	60	62	30
UCTS1-72PG	Conduit Trapeze Support, 1 1/4" conduit, PG	72	74	36

Note: All dimensions and weights are subject to normal manufacturing tolerances.

Certifications:

- UL listed for US and Canada
- Most configurations exceed maximum load ratings defined by UL requirements
- 500 lb. load rating at 12"
- Hanger spacing for all three sizes
- Safety factor of 3





Conduit Trapeze Support - Up to 2" Conduit

Part Number	Description	Nominal Length	A	Conduit Hole
		in	in	
UCTS2-12PG	Conduit Trapeze Support, 2" conduit, PG	12	14	4
UCTS2-24PG	Conduit Trapeze Support, 2" conduit, PG	24	26	8
UCTS2-36PG	Conduit Trapeze Support, 2" conduit, PG	36	38	12
UCTS2-48PG	Conduit Trapeze Support, 2" conduit, PG	48	50	16
UCTS2-60PG	Conduit Trapeze Support, 2" conduit, PG	60	62	20
UCTS2-72PG	Conduit Trapeze Support, 2" conduit, PG	72	74	24

Note: All dimensions and weights are subject to normal manufacturing tolerances.

Certifications:

- UL listed for US and Canada
- Most configurations exceed maximum load ratings defined by UL requirements
- 500 lb. load rating at 12"
- Hanger spacing for all three sizes
- Safety factor of 3



Conduit Trapeze Support - Up to 4" Conduit

Part Number	Description	Nominal Length	A	Conduit Hole
		in	in	
UCTS4-12PG	Conduit Trapeze Support, 4" conduit, PG	12	14	2
UCTS4-24PG	Conduit Trapeze Support, 4" conduit, PG	24	26	4
UCTS4-36PG	Conduit Trapeze Support, 4" conduit, PG	36	38	6
UCTS4-48PG	Conduit Trapeze Support, 4" conduit, PG	48	50	8
UCTS4-60PG	Conduit Trapeze Support, 4" conduit, PG	60	62	10
UCTS4-72PG	Conduit Trapeze Support, 4" conduit, PG	72	74	12

Note: All dimensions and weights are subject to normal manufacturing tolerances.

Certifications:

- UL listed for US and Canada
- Most configurations exceed maximum load ratings defined by UL requirements
- 500 lb. load rating at 12"
- Hanger spacing for all three sizes
- Safety factor of 3

