


SOLUTIONS FOR YOUR WIRING APPLICATIONS



AFC MC-Plus Neutral Per Phase - Type MC Cable

Individual neutrals for each phase conductor. Insulated copper grounding conductor.

Meets NEC 210.4(B) Disconnecting Means, Meets NEC 300.22 (C) Environmental Air Handling Spaces (Plenum ceilings and under raised floors.)

Steel Armor - Solid Conductors

250' Coils	1000' Reels	Phase	Neutrals	Ground	Approximate Weight (lbs)/1000 (ft)	Armor O.D. (in)
3904-42-00	3904-60-00	12-2	12-2	12-1	233	0.586
3904-42-01	3904-60-01	12-2	12-2	12-1	233	0.586
3904-42-02	3904-60-02	12-2	12-2	12-1	233	0.586
3904-42-03	3904-60-03	12-2	12-2	12-1	233	0.586
3904-42-04	3904-60-04	12-2	12-2	12-1	233	0.586
3904-42-05	3904-60-05	12-2	12-2	12-1	233	0.586
3905-42-00	3905-60-00	12-3	12-3	12-1	306	0.620
3905-42-01	3905-60-01	12-3	12-3	12-1	306	0.620
3906-42-00	3906-60-00	12-4	12-4	12-1	380	0.698
3907-42-00	3907-60-00	10-2	10-2	10-1	326	0.667
3907-42-01	3907-60-01	10-2	10-2	10-1	326	0.667
3908-42-00	3908-60-00	10-3	10-3	10-1	433	0.710
3908-42-01	3908-60-01	10-3	10-3	10-1	433	0.710
3909-42-00	3909-60-00	10-4	10-4	10-1	570	0.856
3914-42-00	3914-60-00	10-6	10-6	10-1	761	0.979



For more info visit atkore.com/afc 

Aluminum Armor - Solid Conductors

250' Coils	1000' Reels	Phase	Neutrals	Ground	Approximate Weight (lbs)/1000 (ft)	Armor O.D. (in)
3604-42-00	3604-60-00	12-2	12-2	12-1	169	0.586
3604-42-01	3604-60-01	12-2	12-2	12-1	169	0.586
3605-42-00	3605-60-00	12-3	12-3	12-1	241	0.620
3605-42-01	3605-60-01	12-3	12-3	12-1	241	0.620

Aluminum Armor - Stranded Conductors

250' Coils	1000' Reels	Phase	Neutrals	Ground	Approximate Weight (lbs)/1000 (ft)	Armor O.D. (in)
3658-42-00	3658-60-00	12-2	12-2	12-1	169	0.613
3658-42-01	3658-60-01	12-2	12-2	12-1	169	0.613
3659-42-00	3659-60-00	12-3	12-3	12-1	241	0.613
3659-42-01	3659-60-01	12-3	12-3	12-1	241	0.613
3661-42-00	3661-60-00	10-2	10-2	10-1	255	0.704
3661-42-01	3661-60-01	10-2	10-2	10-1	255	0.704
3662-42-00	3662-60-00	10-3	10-3	10-1	347	0.805
3662-42-01	3662-60-01	10-3	10-3	10-1	347	0.805
3663-42-00	3663-60-00	10-4	10-4	10-1	442	0.911

MC-Plus Conductor Color Coding

Two Wire	Phase Colors	Neutrals
-00	Black, Red	2 Whites
-01	Brown, Orange	2 Grays
-02	Orange, Yellow	2 Grays
-03	Brown, Yellow	2 Grays
-04	Red, Blue	2 Whites
-05	Black, Blue	2 Whites