



PVC AWWA C900 Pressure Pipe

Conforms to AWWA C900

- Conforms to UL1285 as listed by NSF in accordance with Standard NSF14
- Listed to FM 1612 for DR 14 and DR 18 products
- Each spigot end is beveled to facilitate assembly and double reference marked to indicate proper insertion depth
- Product manufactured with one integral gasketed bell per length
- Standard laying length of pipe is 20 feet
- Standard color is blue
- Green and purple are available upon request



Trade Size	Part Number	Dimensions (in)		Minimum Wall Thickness (in)	Approximate Weight per 100' (lbs)	Crate Quantity (ft)
		Average OD	Bell Depth			
DR 25 - Pressure Rating 165 psi						
4	3640020G	4.800	5.50	0.192	191	960
6	3660020G	6.900	6.25	0.276	395	280
8	3680020G	9.050	7.50	0.362	683	200
10	36100020G	11.100	8.75	0.444	1,034	160
12	36120020G	13.200	9.25	0.527	1,465	60
DR 18 - Pressure Rating 235 psi* 						
4	3740020G	4.800	5.50	0.267	261	960
6	3760020G	6.900	6.25	0.383	541	280
8	3780020G	9.050	7.50	0.502	936	200
10	37100020G	11.100	8.75	0.616	1,417	160
12	37120020G	13.200	9.25	0.733	2,010	60
DR 14 - Pressure Rating 305 psi* 						
4	3840020G	4.800	5.50	0.343	330	960
6	3860020G	6.900	6.25	0.493	686	280
8	3880020G	9.050	7.50	0.646	1,187	200
10	38100020G	11.100	8.75	0.793	1,799	160
12	38120020G	13.200	9.25	0.943	2,553	60

*FM pressure rating is 250 psi for DR 14 and 185 psi for DR 18



For more info visit atkore.com/heritageplastics