

MATERIAL SAFETY DATA SHEET

Thread Compound



Atkore[™]
Calbond



KOPR KOTE® INDUSTRIAL

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Issue date: 03/13/2020

Version: 1.0

SECTION 1: Identification

1.1. Identification

Product form : Mixture
Product name : KOPR KOTE® INDUSTRIAL

1.2. Recommended use and restrictions on use

Use of the substance/mixture : HIGH TEMPERATURE ANTI-SEIZE
Use of the substance/mixture : Lubricant

1.3. Supplier

Manufacturer

Jet-Lube
930 Whitmore Drive
Rockwall, Texas 75087 - USA
T 1.972.771.1000
Regulatory@whitmores.com - www.jetlube.com

1.4. Emergency telephone number

Emergency number : For Chemical Emergency Call CHEMTREC 24hr/day 7days/week
Within USA and Canada: 1.800.424.9300
Outside USA and Canada: +1.703.527.3887
(collect calls accepted)

SECTION 2: Hazard(s) identification

2.1. Classification of the substance or mixture

GHS US classification

Serious eye damage/eye irritation Category 2A H319 Causes serious eye irritation

Full text of H statements : see section 16

2.2. GHS Label elements, including precautionary statements

GHS US labeling

Hazard pictograms (GHS US) :



Signal word (GHS US) : Warning
Hazard statements (GHS US) : H319 - Causes serious eye irritation
Precautionary statements (GHS US) : P264 - Wash hands thoroughly after handling.
P280 - Wear eye protection, protective gloves.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 - If eye irritation persists: Get medical advice/attention.

2.3. Other hazards which do not result in classification

No additional information available

2.4. Unknown acute toxicity (GHS US)

Not applicable

SECTION 3: Composition/Information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	GHS US classification
Distillates (petroleum), hydrotreated heavy naphthenic	(CAS-No.) 64742-52-5	30 - 40	Not classified
Copper	(CAS-No.) 7440-50-8	5 - 10	Not classified

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Name	Product identifier	%	GHS US classification
Calcium dodecylbenzenesulfonate	(CAS-No.) 26264-06-2	1 - 5	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318

Full text of hazard classes and H-statements : see section 16

SECTION 4: First-aid measures

4.1. Description of first aid measures

- First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.
- First-aid measures after skin contact : Wash skin with plenty of water.
- First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
- First-aid measures after ingestion : Call a poison center/doctor/physician if you feel unwell.

4.2. Most important symptoms and effects (acute and delayed)

- Symptoms/effects after eye contact : Eye irritation.

4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

- Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

5.2. Specific hazards arising from the chemical

- Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Special protective equipment and precautions for fire-fighters

- Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

- Emergency procedures : Exercise caution. Spill area may be slippery. Avoid contact with skin and eyes.

6.1.2. For emergency responders

- Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : Take up liquid spill into absorbent material.
- Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Wear personal protective equipment.
- Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Store in a well-ventilated place. Keep cool.

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

KOPR KOTE® INDUSTRIAL	
No additional information available	
Distillates (petroleum), hydrotreated heavy naphthenic (64742-52-5)	
No additional information available	
Copper (7440-50-8)	
USA - ACGIH - Occupational Exposure Limits	
Local name	Copper, as Cu
ACGIH TWA (mg/m ³)	0.2 mg/m ³ (Fume) 1 mg/m ³ (Dusts and mists)
Remark (ACGIH)	TLV® Basis: Irr; GI; metal fume fever
Regulatory reference	ACGIH 2019
USA - OSHA - Occupational Exposure Limits	
Local name	Copper
OSHA PEL (TWA) (mg/m ³)	0.1 mg/m ³ (Fume (as Cu)) 1 mg/m ³ (Dusts and mists (as Cu))
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1
Calcium dodecylbenzenesulfonate (26264-06-2)	
No additional information available	

8.2. Appropriate engineering controls

- Appropriate engineering controls : Ensure good ventilation of the work station.
 Environmental exposure controls : Avoid release to the environment.

8.3. Individual protection measures/Personal protective equipment

Hand protection:

Protective gloves. Neoprene or nitrile rubber gloves

Eye protection:

Chemical goggles or safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Paste.
Color	: Metallic
Odor	: Petroleum-like odour
Odor threshold	: No data available
pH	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 221 °C Open Cup
Relative evaporation rate (butyl acetate=1)	: No data available
Flammability (solid, gas)	: Not applicable.
Vapor pressure	: No data available

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Relative vapor density at 20 °C	: No data available
Relative density	: No data available
Specific gravity / density	: 1.15
Solubility	: insoluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity, kinematic	: > 25 mm ² /s @ 40°C
Viscosity, dynamic	: No data available
Explosion limits	: No data available
Explosive properties	: No data available
Oxidizing properties	: No data available

9.2. Other information

VOC content : 0 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

Distillates (petroleum), hydrotreated heavy naphthenic (64742-52-5)

LD50 oral rat	> 5000 mg/kg body weight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity), Guideline: OECD Guideline 420 (Acute Oral Toxicity - Fixed Dose Method)
LD50 dermal rat	> 5000 mg/kg Sufficiently refined

Copper (7440-50-8)

LD50 oral rat	> 2500 mg/kg body weight (OECD 423: Acute Oral Toxicity – Acute Toxic Class Method, Rat, Male, Experimental value, Oral, 14 day(s))
LD50 dermal rat	> 2000 mg/kg body weight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity), Guideline: EU Method B.3 (Acute Toxicity (Dermal)), Guideline: EPA OTS 798.1100 (Acute Dermal Toxicity), Guideline: other:MAFF 4200 (1985)
LC50 inhalation rat (mg/l)	> 5.11 mg/l air Animal: rat, Guideline: OECD Guideline 436 (Acute Inhalation Toxicity: Acute Toxic Class Method)

Calcium dodecylbenzenesulfonate (26264-06-2)

LD50 oral rat	1300 mg/kg
LD50 dermal rabbit	> 2000 mg/kg
ATE US (oral)	1300 mg/kg body weight

Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitization	: Not classified

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified.
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified.

Distillates (petroleum), hydrotreated heavy naphthenic (64742-52-5)

LOAEL (oral, rat, 90 days)	125 mg/kg body weight Animal: rat, Animal sex: male, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)
----------------------------	--

Aspiration hazard	: Not classified
Viscosity, kinematic	: > 25 mm ² /s @ 40°C
Symptoms/effects after eye contact	: Eye irritation.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.
-------------------	--

Copper (7440-50-8)

LC50 fish 1	38.4 – 256.2 µg/l (96 h, Pimephales promelas, Flow-through system, Fresh water, Read-across)
EC50 Daphnia 1	3.8 – 118.5 µg/l (US EPA, 48 h, Daphnia magna, Static system, Fresh water, Weight of evidence)

12.2. Persistence and degradability

Copper (7440-50-8)

Persistence and degradability	Biodegradability: not applicable.
Chemical oxygen demand (COD)	Not applicable
ThOD	Not applicable
BOD (% of ThOD)	Not applicable

12.3. Bioaccumulative potential

Copper (7440-50-8)

Bioaccumulative potential	Bioaccumulation: not applicable.
---------------------------	----------------------------------

12.4. Mobility in soil

Copper (7440-50-8)

Ecology - soil	Adsorbs into the soil.
----------------	------------------------

12.5. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Disposal methods

Waste treatment methods	: Dispose of contents/container in accordance with licensed collector's sorting instructions.
-------------------------	---

SECTION 14: Transport information

Department of Transportation (DOT)

In accordance with DOT

Not regulated

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Transport by sea

Not regulated

Air transport

Not regulated

SECTION 15: Regulatory information

15.1. US Federal regulations

All components of this product are listed, or excluded from listing, on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

Chemical(s) subject to the reporting requirements of Section 313 or Title III of the Superfund Amendments and Reauthorization Act (SARA) of 1986 and 40 CFR Part 372.

Copper	CAS-No. 7440-50-8	5 - 10%
Copper (7440-50-8)		
CERCLA RQ	5000 lb	
Calcium dodecylbenzenesulfonate (26264-06-2)		
CERCLA RQ	1000 lb	

15.2. International regulations

CANADA

Distillates (petroleum), hydrotreated heavy naphthenic (64742-52-5)
Listed on the Canadian DSL (Domestic Substances List)
Copper (7440-50-8)
Listed on the Canadian DSL (Domestic Substances List)
Calcium dodecylbenzenesulfonate (26264-06-2)
Listed on the Canadian DSL (Domestic Substances List)

EU-Regulations

National regulations

No additional information available

15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

SECTION 16: Other information

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Full text of H-phrases:

H302	Harmful if swallowed
H315	Causes skin irritation
H318	Causes serious eye damage
H319	Causes serious eye irritation

SDS US (GHS HazCom 2012)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.



Allied Tube & Conduit ▸ AFC Cable Systems ▸ Heritage Plastics ▸ Unistrut
Unistrut Construction ▸ Cope ▸ US Tray ▸ Calbrite ▸ Calbond ▸ Kaf-Tech
Columbia-MBF ▸ Eastern Wire + Conduit ▸ ACS/Uni-Fab ▸ Cii
Power-Strut ▸ Calconduit ▸ Razor Ribbon ▸ Calpipe Security
FRE Composites ▸ Vergokan ▸ Flexicon ▸ Marco

Atkore
12160 Woodruff Ave.
Downey, CA 90241

PHONE / 562-803-4388
TOLL FREE / 800-225-7473

calbond.com

Want to join a company that helps you build
the mindset, skill set and tool set for success?
Visit us at atkore.com/careers