

# RAISED ACCESS FLOOR BOX HIGH CAPACITY 2000




Independent tests confirm, this is the most air tight floor box we have ever made. With zero air leakage, no one can do better!

Leaky air ruins the efficiency of HVAC systems and creates uncomfortable work spaces. Our zero air leakage box allows your HVAC to run at peak efficiency and keeps your people happy.

## Features

- General purpose, isolated ground and/or dedicated circuits multi-purpose workstations
- Fully hot swappable with Powermate plug and play system
- Quick relocation when used with the Cii plug and play modular wiring system
- Consolidation of power, voice and data in a common enclosure with effective wire management
- 4 Duplexes
- 3 Trade size single gang openings for the networking
- Cable management loop



For more info visit [atkore.com/cii](https://atkore.com/cii)




### Three things make our floor box air tight:


- 1) A gasket between floor and box keeps air from leaking around the sides.
- 2) Our “green seal” makes the lid air tight.
- 3) Brushes seal the gaps around power and network cables.

## Specifications


- Zero air leakage
- 11 $\frac{3}{4}$ " Square lid assembly
- $\frac{3}{16}$ " Thin low profile trim frame
- 4 $\frac{7}{8}$ " Overall depth for 5" minimum floor height
- Configurable for up to 4 duplexes and 18 RJ45 network jacks
- 2000 lb lid load rating
- Up to 6 circuits



Cutaway with Dimensions



Up to 2000 lb Load



Floor Cut Dimensions