



MC GLIDE LUMINARY TUFF CABLE

Type MC-PCS

U.S. Patent 11,101,056 | U.S. Design Patent D935,731 | U.S. Patent 10,431,353

Armor

Galvanized Interlocked Steel Strip (Blue)

Conductors

Solid/Stranded Copper

Conductor Insulation

THHN (Power)

TFN (Control)

Maximum Temperature Rating

90°C (Dry)

Neutral Conductor

White 120/208V

Gray 277/480V

Control Cables

16 AWG Solid TFN Twisted Pink Jacketed pair (Purple/Pink)

Maximum Voltage Rating

600V

Reference & Rating

- UL 66, 83, 1479, 1569, 1581, 2556, File Reference E80042
- NEC® 250.118(I), 300.22(C), 330, 392, 396, 501, 502, 503, 504, 505, 518, 520, 530, 645, 725.136(I)(1)
- Permits conductors of control circuits to be placed in a cable with conductors of electric light, power, or Class 1 circuits
- Federal Specification A-A-59544 (formerly J-C-30B)
- Meets all applicable OSHA and HUD Requirements
- Cable Tray Rated, install per NEC®
- UL Classified 1, 2, and 3 hour through penetration (Fire Stop) product, R14141
- NEC® 300.22(C) other spaces used for environmental air (plenums)
- Power and/or lighting as well as signal and/or control conductors per NEC® Section 725.136(I)(1)
- May be surface mounted, fished and/or embedded in plaster
- Made in USA of US and/or imported materials

Product Code		Trade Size	Grounding Conductor AWG	Approx. Weight	Approx. Armor O.D.
250' Coil	1000' Reel			lbs/1,000ft	(in)
Solid					
SL04B42-L00	SL04B60-L00	16-2 (TPJ) (Purple, Pink) 12-2 (Black, White)	12-1 (Green)	208	0.560
SL04B42-L01	SL04B60-L01	16-2 (TPJ) (Purple, Pink) 12-2 (Brown, Gray)	12-1 (Green)	208	0.560
SL04B42-L02	SL04B60-L02	16-2 (TPJ) (Purple, Pink) 12-2 (Orange, Gray)	12-1 (Green)	208	0.560
SL04B42-L03	SL04B60-L03	16-2 (TPJ) (Purple, Pink) 12-2 (Yellow, Gray)	12-1 (Green)	208	0.560
SL04B42-L04	SL04B60-L04	16-2 (TPJ) (Purple, Pink) 12-2 (Red, White)	12-1 (Green)	208	0.560
SL04B42-L05	SL04B60-L05	16-2 (TPJ) (Purple, Pink) 12-2 (Blue, White)	12-1 (Green)	208	0.560
SL04B42-L07*	SL04B60-L07*	16-2 (TPJ) (Purple, Pink) 12-2 (Purple, Gray)	12-1 (Green)	208	0.560

All dimensions and weights are subject to normal manufacturing tolerances.

Other conductor colors available by special order.

*Non-stock items require lead time and minimum quantity order.

MC Luminary Cable is intended for use in non-shielded applications

