



ATKORE DEFENDER™

Corrosion Resistant Metal Framing Line Electrical Submittal Package

Alterations to this document by any agency other than Atkore International voids the certification.



Atkore™
Unistrut


Corrosion Protection



Atkore Defender™

Atkore Defender is designed for harsh environments, providing a service life between Hot-Dip Galvanized and stainless steel systems. Independent testing shows that Atkore Defender is **THREE** times more corrosion-resistant than Hot-Dip Galvanized products. In addition, Atkore Defender avoids the use of costly stainless steel hardware. Atkore Defender is a great choice for harsh and corrosive environments.

Get better performance with Atkore Defender. This brochure lists the Unistrut Defender parts, dimensions and applications that are commonly in stock. Many other Unistrut parts can be made by request. For more information about Atkore Defender, contact your Atkore Regional Sales Manager, Agent or call 800-882-5543.



The Atkore Defender coating was tested against the traditional Hot-Dip Galvanized coating by an independent, accredited 3rd party laboratory for 3,000 hours of continuous salt spray exposure per ASTM B117. The test was conclusive, proving that

Atkore Defender outperforms Hot-Dip Galvanizing by lasting 3 times as long before reaching the 5% red rust failure criteria! **The photos below show the clearly superior performance provided by Atkore Defender.**


PHOTOS FROM ASTM B117 SALT SPRAY TEST

	0 hours	100 hours	1,000 hours	2,000 hours	3,000 hours
Atkore Defender™ (DF)					
Hot-Dip Galvanized (HG) per ASTM A123 and A153					

With over 3 times the corrosion protection of Hot-Dip Galvanized products, the anticipated service life for Atkore Defender vastly outperforms traditional carbon steel framing systems.


Atkore Defender will meet the design life of most new applications, eliminating the need to replace parts over time. See the difference below!

ANTICIPATED SERVICE LIFE (Time to 5% Red Rusting of the Steel Surface)



*Hot-Dip Galvanized per ASTM A123 and A153 coating service life as specific within the North American Metal Framing Industry

TYPICAL APPLICATION DESIGN LIFE¹ VS. ANTICIPATED SERVICE LIFE



¹) Typical application design life is sourced from a number of different publications and is not true for all applications. Reference your project-specific requirements and environment for a true performance estimate.

²) Hot-Dip Galvanized per ASTM A123 and A153 coating service life as specific within the North American Metal Framing Industry

Finishes:

Atkore Defender is a combination of two proprietary material coatings conforming to ASTM standards A1046 and A1059.

Materials:

Channel, Fittings and Pipe Clamps meet the physical requirements of ASTM A1011 SS GR 33.

Technical Notes:

1. Structural performance, including Slip and Pull-Out Loads, meets all Allowable Loads as specified in the Unistrut General Engineering catalog for carbon steels. Please reference the Unistrut General Engineering catalog for this information.
2. To achieve full performance and cost benefits, Atkore Defender must be used as a complete metal framing system. In addition, caution should be taken when putting Atkore Defender in contact with stainless steel materials due to a dissimilar metals condition that may cause galvanic corrosion.
3. Some red staining may be observed over time on Atkore Defender parts in corrosive environments. Red staining is superficial oxidation of the zinc/iron ions at the surface, and not corrosion of the substrate steel. This is noted in ASTM A1059 section 6.3.
4. One of the unique characteristics of Atkore Defender strut channel is that it contains self-healing properties. If the product is cut or scratched in the field, the finish will propagate into those areas eliminating the need for secondary touch-ups.



1 5/8" Channel

P1000 DF (12 Gauge).....	6
P3300 DF (12 Gauge).....	7
P4100 DF (14 Gauge).....	8
P5000 DF (12 Gauge).....	9

Nuts & Hardware

Channel Nuts With Springs.....	10
Channel Nuts Without Springs.....	10
Hardware.....	10

General Fittings & Beam Clamps

General Fittings.....	12
Beam Clamps.....	15

Pipe/Conduit Supports



Pipe/Conduit Clamps.....	16
--------------------------	----



1 5/8" Channel



P1000® DF & P1001 DF Channels

P1000 DF



Wt/100 ft: 189 lbs (281 kg/100 m)
Allowable Moment 5,070 in-lbs (570 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)


P1001 DF



Wt/100 ft: 378 lbs (562 kg/100 m)
Allowable Moment 14,360 in-lbs (1,620 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)


P1000T DF

Slots are
1 1/8" (28.6) x 9/16" (14.3)
2" (50.8) on Center



Wt/100 ft: 185 lbs (275 kg/100 m)

P1001T DF



Wt/100 ft: 321 lbs (478 kg/100 m)
Allowable Moment 12,200 in-lbs (1,378 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)

Channel Nuts (Refer to Hardware Section for Details)



P1006-1420 DF
P1008 DF
P1010 DF




P3006-1420 DF
P3008 DF
P3010 DF

Standard Channel Lengths: 10' & 20'



1 5/8" Channel

P1000 DF (12 Gauge).....	6
P3300 DF (12 Gauge).....	7
P4100 DF (14 Gauge).....	8
P5000 DF (12 Gauge).....	9



Standard Lengths


Standard lengths are 10 feet (3.05m) and 20 feet (6.10m). Tolerances are ±1/8" (3 mm). Special lengths are available for a small cutting charge with a tolerance of ±1/8" (3 mm).

Dimensions

Imperial dimensions are illustrated in inches. Metric dimensions are shown in millimeters and rounded to one decimal place.

Nuts & Hardware

Channel Nuts With Springs	10
Channel Nuts Without Springs	10
Hardware	10



Threads


All threads on the nuts and bolts are Unified and American coarse screw threads.

Dimensions

Imperial dimensions are illustrated in inches. Metric dimensions are shown in parentheses or as noted. Unless noted, all metric dimensions are in millimeters and rounded to one decimal place.

General Fittings & Beam Clamps

General Fittings	12
Beam Clamps	15



Application

All parts drawings illustrate only one application of each fitting. In most cases many other applications are possible. The channels shown in the illustrations are P1000, 1 5/8" square, except where noted otherwise.


All 9/16" diameter holes use 1/2" x 1 3/16" hex head cap screws and 1/2" nuts - P1010, P4010 or P5510 - depending on the channel used.

Beam Clamps

Clamps are designed to be used with W, M, S and HP Shape beams, Standard C and Miscellaneous MC Channels, Angles and Structural Tees. Clamps must be used in pairs where indicated.

Pipe/Conduit Supports

Pipe/Conduit Clamps	16
---------------------------	----



Application

Unistrut pipe clamps are designed for the support of electrical and mechanical services. Supports to meet nearly every requirement can be attained using Unistrut Metal Framing components.



Dimensions

Imperial dimensions are illustrated in inches. Metric dimensions are shown in parenthesis or as noted. Unless noted, all metric dimensions are in millimeters and rounded to one decimal place.

1 5/8" Channel



P1000® DF & P1001 DF Channels

P1000 DF



Wt/100 ft: 189 lbs (281 kg/100 m)
Allowable Moment 5,070 in-lbs (570 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)


P1001 DF



Wt/100 ft: 378 lbs (562 kg/100 m)
Allowable Moment 14,360 in-lbs (1,620 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)


P1000T DF

Slots are
1 1/8" (28.6) x 9/16" (14.3)
2" (50.8) on Center



Wt/100 ft: 185 lbs (275 kg/100 m)

P1001T DF



Wt/100 ft: 321 lbs (478 kg/100 m)
Allowable Moment 12,200 in-lbs (1,378 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)

Channel Nuts (Refer to Hardware Section for Details)



P1006-1420 DF
P1008 DF
P1010 DF





P3006-1420 DF
P3008 DF
P3010 DF

Standard Channel Lengths: 10' & 20'





P3300® DF & P3301 DF Channels

P3300 DF




P3301 DF




P3300T DF

Slots are
1 1/8" (28.6) x 9/16" (14.3)
2" (50.8) on Center



Wt/100 ft: 130 lbs (193 kg/100 m)

P3301T DF





Channel Nuts (Refer to Hardware Section for Details)





Standard Channel Lengths: 10' & 20'

P4100® DF & P4101 DF Channels

P4100 DF




P4101 DF



P4100T DF


Slots are
1 1/8" (28.6) x 9/16" (14.3)
2" (50.8) on Center



Wt/100 ft: 87 lbs (129 kg/100 m)

P4101T DF

Slots are
1 1/8" (28.6) x 9/16" (14.3)
2" (50.8) on Center



Wt/100 ft: 174 lbs (259 kg/100 m)

Channel Nuts (Refer to Hardware Section for Details)




Standard Channel Lengths: 10' & 20'




P5000® DF & P5001 DF Channels

P5000 DF



Wt/100 ft: 305 lbs (454 kg/100 m)
Allowable Moment 15,770 in-lbs (1,780 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)


P5001 DF



Wt/100 ft: 610 lbs (907 kg/100 m)
Allowable Moment 48,180 in-lbs (5,440 N·m)
12 Gauge Nominal Thickness .105" (2.7mm)


P5000T DF

Slots are
1 1/8" (28.6) x 9/16" (14.3)
2" (50.8) on Center




Wt/100 ft: 300 lbs (446 kg/100 m)

P5001T DF



Wt/100 ft: 600 lbs (892 kg/100 m)

Channel Nuts (Refer to Hardware Section for Details)




Standard Channel Lengths: 10' & 20'

Nuts & Hardware


Channel Nuts With and Without Spring

Channel Nut With Spring



Part Number	Nut Size	Thread	Wt/100 pcs lbs (kg)	Use With
P1006-1420 DF	1/4"	-20	7 (3.2)	P1000 DF
P1008 DF	3/8"	-16	10 (4.5)	
P1010 DF	1/2"	-13	12 (5.4)	
P4008 DF	3/8"	-16	9 (4.1)	P3300 DF, P4100 DF
P4010 DF	1/2"	-13	8 (3.6)	
P5508 DF	3/8"	-16	10 (4.5)	P5000 DF
P5510 DF	1/2"	-13	12 (5.4)	


Channel Nut Without Spring



Part Number	Nut Size	Thread	Wt/100 pcs lbs (kg)	Use With
P3006-1420 DF	1/4"	-20	6 (2.7)	Any Channel
P3008 DF	3/8"	-16	9 (4.1)	
P3010 DF	1/2"	-13	11 (5.0)	P1000 DF, P4100 DF
P3013 DF	1/2"	-13	8 (3.6)	P3300 DF, P4100 DF

Hardware

HEX Head Cap Screws



Part Number	Size	Wt/100 pcs lbs (kg)
HHCS025075DF	1/4" x 3/4"	1.3 (0.6)
HHCS025150DF	1/4" x 1 1/2"	2.6 (1.2)
HHCS037100DF	3/8" x 1"	4.5 (2.0)
HHCS037150DF	3/8" x 1 1/2"	6.0 (2.7)
HHCS050094DF	1/2" x 1 5/16"	9.1 (4.1)
HHCS050119DF	1/2" x 1 3/8"	10.2 (4.6)
HHCS050150DF	1/2" x 1 1/2"	11.6 (5.3)

Hexagon Nuts



Part Number	Size	Wt/100 pcs lbs (kg)
HHXN025DF	1/4"	0.6 (0.3)
HHXN037DF	3/8"	1.6 (0.7)
HHXN050DF	1/2"	4.8 (2.2)


Flat Washers



Part Number	Size	Wt/100 pcs lbs (kg)
HFLW025DF	1/4"	0.8 (0.4)
HFLW037DF	3/8"	1.5 (0.7)
HFLW050DF	1/2"	3.5 (1.6)




Hardware



Steel Coupler Nuts

Part Number	Size	Length (mm)	Wt/100 pcs lbs (kg)
HRCN037DF	3/8" - 16	1 3/4" (44.5)	9.0 (4.1)
HRCN050DF	1/2" - 13	1 3/4" (44.5)	10.0 (4.5)



Steel Threaded Rod

Part Number	Size	Wt/100 pcs lbs (kg)
HTHR037DF	3/8" - 16	30 (13.6)
HTHR050DF	1/2" - 13	53 (24.0)

Low Carbon Steel Grade 1006 - 1010
 Fy = 36,000 psi minimum
 Ft = 58,000 psi minimum


Standard Length 6' (1.83m)

Lock Washers




Part Number	Size	Wt/100 pcs lbs (kg)
HLKW025DF	1/4"	0.25 (0.1)
HLKW037DF	3/8"	0.63 (0.3)
HLKW050DF	1/2"	1.32 (0.60)

General Fittings



P1063 DF, P1064 DF


Part Number	Bolt Size	Hole Size	Wt/100 pcs lbs (kg)
P1063 DF	3/8"	7/16"	18 (8.2)
P1064 DF	1/2"	9/16"	17 (7.7)



P2863 DF, P2864 DF


Part Number	Bolt Size	Hole Size	Wt/100 pcs lbs (kg)
P2863 DF	3/8"	7/16"	18 (8.2)
P2864 DF	1/2"	9/16"	17 (7.7)

P1065 DF




Wt/100 pcs: 38 lbs (17.2 kg)

P2324 DF




Wt/100 pcs: 75 lbs (34.0 kg)

P1066 DF




Wt/100 pcs: 56 lbs (25.4 kg)

P1067 DF




Wt/100 pcs: 78 lbs (35.4 kg)

P1036 DF



Wt/100 pcs: 58 lbs (26.3 kg)

P1380A DF




Wt/100 pcs: 105 lbs (47.6 kg)

Standard Dimensions for 15/8" (41.3mm) width series channel fittings (Unless Otherwise Shown on Drawing)
 Hole Diameter: 9/16" (14.3mm); Hole Spacing - From End: 13/16" (20.6mm); Hole Spacing - On Center: 17/8" (47.6mm); Width: 15/8" (41.3mm); Thickness: 1/4" (6.4mm)




General Fittings

P1031 DF




Wt/100 pcs: 80 lbs (36.3 kg)

P1028 DF




Wt/100 pcs: 105 lbs (47.6 kg)

P1026 DF




Wt/100 pcs: 38 lbs (17.2 kg)

P1068 DF




Wt/100 pcs: 38 lbs (17.2 kg)

P1346 DF




Wt/100 pcs: 58 lbs (26.3 kg)

P1325 DF




Wt/100 pcs: 78 lbs (35.4 kg)

P2484 DF




Wt/100 pcs: 134 lbs (60.8 kg)



P1498 DF

Part Number	"A" in (mm)	"B" in (mm)	Wt/100 pcs lbs (kg)
P1498 DF	4 7/8"	2 1/2"	65 (29.5)




P1546 DF

Part Number	"A" in (mm)	"B" in (mm)	"C" in (mm)
P1546 DF	45° (0.79)	3 (76.2)	2 5/16 (58.7)

Wt/100 pcs: 58 lbs (26.3 kg)


Standard Dimensions for 15/8" (41.3mm) width series channel fittings (Unless Otherwise Shown on Drawing)
Hole Diameter: 9/16" (14.3mm); Hole Spacing - From End: 13/16" (20.6mm); Hole Spacing - On Center: 17/8" (47.6mm); Width: 15/8" (41.3mm); Thickness: 1/4" (6.4mm)

General Fittings




P1186 DF

Part Number	"A" in (mm)	"B" in (mm)
P1186 DF	45° (0.79)	3 1/8" (79.4)



P2265 DF


Part Number	"A" in (mm)	"B" in (mm)
P2265 DF	45° (0.79)	3 1/16" (93.7)



P1048 DF


Part Number	"A" in (mm)	"B" in (mm)	Wt/100 pcs lbs (kg)
P1048 DF	7 1/4 (184.2)	4 1/8" (104.8)	105 (47.6)

P1045 DF






Wt/100 pcs: 55 lbs (24.9 kg)

P1047 DF



Wt/100 pcs: 88 lbs (39.9 kg)

P2072A DF, P2072A SQ DF




Wt/100 pcs: 373 lbs (169.2 kg)

Standard Dimensions for 15/8" (41.3mm) width series channel fittings (Unless Otherwise Shown on Drawing)
Hole Diameter: 9/16" (14.3mm); Hole Spacing - From End: 13/16" (20.6mm); Hole Spacing - On Center: 17/8" (47.6mm); Width: 15/8" (41.3mm); Thickness: 1/4" (6.4mm)



General Fittings

P1271S DF




Wt/100 pcs: 95 lbs (43.1 kg)

Design Load Each
500 lbs (2.22 kN)
Use in Pairs Only

Note: Requires P1010
Channel Nut and bolt.

P2785 DF




Wt/100 pcs: 83 lbs (37.6 kg)

Design Load Each
1,000 lbs (4.45 kN)
Use in Pairs Only

• For use with Beams
up to 3/4" (19.1) Flanges
and with Channels
P1000, P3300, P3301,
P4100, and P4101.

P2786 DF




Wt/100 pcs: 92 lbs (41.7 kg)

Design Load Each
1,000 lbs (4.45 kN)
Use in Pairs Only

• For use with Beams
up to 3/4" (19.1) Flanges
and with Channels
P1001, P5000.

P2787 DF




Wt/100 pcs: 112 lbs (50.8 kg)

Design Load Each
1,000 lbs (4.45 kN)
Use in Pairs Only

• For use with Beams
up to 3/4" (19.1) Flanges
and with Channels
P5001.

Beam Clamps



P1048 DF


Part Number	Design Load Each (Use in Pairs Only) lbs (kN)
P1000 DF	600 (2.67)

Wt/100 pcs: 27 lbs (12.2 kg)

Standard Dimensions for 1 5/8" (41.3mm) width series channel fittings (Unless Otherwise Shown on Drawing)
Hole Diameter: 9/16" (14.3mm); Hole Spacing - From End: 13/16" (20.6mm); Hole Spacing - On Center: 17/8" (47.6mm); Width: 1 5/8" (41.3mm); Thickness: 1/4" (6.4mm)
Note: When used for mechanical supports, load capacities of brackets and fittings should be in compliance with the American Standard Code for Pressure Piping.

Pipe/Conduit Clamps


P1428 DF THRU P1431 DF PIPE CLAMPS FOR THIN WALL CONDUIT (E.M.T.)



Part Number	Conduit Size in (mm)	O.D. Size in (mm)	Thickness Gauge (mm)	Wt/100 pcs lbs (kg)	Design Load lbs (kN)
P1428 DF	1 (25.4)	1.163 (29.5)	14 (1.9)	15 (6.8)	600 (2.67)
P1429 DF	1 1/4 (31.8)	1.510 (38.4)	14 (1.9)	18 (8.2)	600 (2.67)
P1430 DF	1 1/2 (38.1)	1.740 (44.2)	12 (2.7)	29 (13.2)	800 (3.56)
P1431 DF	2 (50.8)	2.197 (55.8)	12 (2.7)	33 (15.0)	800 (3.56)
P1118 DF	2 1/2 (63.5)	2.875 (73.0)	12 (2.7)	40 (18.1)	800 (3.56)
P1119 DF	3 (76.2)	3.500 (88.9)	12 (2.7)	47 (21.3)	800 (3.56)

Slotted hex head screw and nut included.


P1112 DF THRU P1119 DF PIPE CLAMPS FOR RIGID STEEL CONDUIT



Part Number	Conduit Size in	O.D. Size in (mm)	Thickness Gauge (mm)	Wt/100 pcs lbs (kg)	Design Load lbs (kN)
P1112 DF	3/4	1.050 (26.7)	14 (1.9)	15 (6.8)	600 (2.67)
P1113 DF	1	1.315 (33.4)	14 (1.9)	17 (7.7)	600 (2.67)
P1114 DF	1 1/4	1.660 (42.2)	14 (1.9)	19 (8.6)	600 (2.67)
P1115 DF	1 1/2	1.900 (48.3)	12 (2.7)	29 (13.2)	800 (3.56)
P1117 DF	2	2.375 (60.3)	12 (2.7)	34 (15.4)	800 (3.56)
P1118 DF	2 1/2	2.875 (73.0)	12 (2.7)	40 (18.1)	800 (3.56)
P1119 DF	3	3.500 (88.9)	12 (2.7)	47 (21.3)	800 (3.56)

Slotted hex head screw and nut included.

P1214 DF THRU P1217 DF UNIVERSAL CLAMPS FOR RIGID OR THINWALL CONDUIT



Part Number	Conduit Size in (mm)	Thickness Gauge (mm)	Wt/100 pcs lbs (kg)	Design Load lbs (kN)
P1214 DF	1 1/4 (31.8)	14 (1.9)	18 (8.2)	600 (2.67)
P1215 DF	1 1/2 (38.1)	14 (1.9)	20 (9.1)	600 (2.67)
P1217 DF	2 (50.8)	14 (1.9)	22 (10.0)	600 (2.67)


Slotted hex head screw and nut included.

HFLW025 DF 10	P1031 DF 13	P1430 DF 16
HFLW037 DF 10	P1036 DF 12	P1431 DF 16
HFLW050 DF 10	P1045 DF 14	P1498 DF 13
HHCS025075DF 10	P1047 DF 14	P1546 DF 13
HHCS025150DF 10	P1048 DF 14	P2072A DF 14
HHCS037100DF 10	P1063 DF 12	P2072ASQ DF 14
HHCS037150DF 10	P1064 DF 12	P2265 DF 14
HHCS050094DF 10	P1065 DF 12	P2324 DF 14
HHCS050119DF 10	P1066 DF 12	P2484 DF 13
HHCS050150DF 10	P1067 DF 12	P2785 DF 15
HHXN025 DF 10	P1068 DF 13	P2786 DF 15
HHXN037 DF 10	P1112 DF 16	P2787 DF 15
HHXN050 DF 10	P1113 DF 16	P2863 DF 12
HLKW025 DF 10	P1114 DF 16	P2864 DF 12
HLKW037 DF 10	P1115 DF 16	P3006-1420DF 6
HLKW050 DF 10	P1117 DF 16	P3008 DF 6
HRCN037 DF 10	P1118 DF 16	P3010 DF 6
HRCN050 DF 11	P1119 DF 16	P3013 DF 7
HTHR037 06DF 11	P1186 DF 14	P3300 DF 7
HTHR050 06DF 11	P1214 DF 16	P3300T DF 7
P1000 DF 6	P1215 DF 16	P4008 DF 7
P1001 DF 6	P1217 DF 16	P4010 DF 7
P1000T DF 6	P1271S DF 15	P4100 DF 8
P1001T DF 6	P1325 DF 13	P4100T DF 8
P1006-1420 DF 6	P1346 DF 13	P5000 DF 10
P1008 DF 6	P1380A DF 12	P5000T DF 10
P1010 DF 6	P1386 DF 15	P5508 DF 9
P1026 DF 13	P1428 DF 16	P5510 DF 9
P1028 DF 13	P1429 DF 16	

Atkore Defender™



Superior Corrosion Defense.



Atkore - UNISTRUT®

This product specification is written according to the Construction Specifications Institute *MasterFormat*, 2018 Update.

SECTION 26 05 29

HANGERS AND SUPPORTS FOR ELECTRICAL SYSTEMS

PART I – GENERAL

1.01 SUMMARY

- A. Framing shall be a strut type metal framing system (Strut System)
- B. Strut System shall be used:
 - 1. To support mechanical and electrical equipment and devices.
 - 2. For structural applications as applicable.
- C. Strut System and components must be supplied from a single approved Manufacturer.

1.02 QUALITY ASSURANCE

- A. Manufacturer's qualifications:
 - 1. The manufacturer shall have at least 10 years' experience in manufacturing Strut Systems.
 - 2. The manufacturer must certify in writing all components supplied have been produced in accordance with an established quality assurance program.
- B. Work shall meet the requirements of the following standards:
 - 1. Federal, State and Local codes
 - 2. American Iron and Steel Institute (AISI) Specification for the Design of Cold-Formed Steel Structural Members 2001 Edition
 - 3. American Society for Testing And Materials (ASTM)
 - 4. Metal Framing Manufacturer's Association (MFMA)

1.03 SUBMITTALS

- A. Structural calculations by a Registered Professional or Structural Engineer in the State of the Project's location for approval by the Professional of Record. Calculations may include, but are not limited to:
 - 1. Description of design criteria
 - 2. Stress and deflection analysis
 - 3. Selection of framing members, fittings, and accessories
- B. Assembly drawings necessary to install the Strut System in compliance with the Contract Drawings
- C. Pertinent manufacturers published data

1.04 PRODUCT DELIVERY, STORAGE, AND HANDLING

- A. All material is to be delivered to the work site in original factory packaging to avoid damage to the finish.
- B. Upon delivery to the work site, all components shall be protected from the elements by a shelter or other covering.

1.05 WARRANTY

- A. Manufacturer shall warrant for 1 year from the shipment date that products will be free from defects in material or manufacture. In the event of any such defect in violation of the warranty, Manufacturer shall have the option to repair or replace any such defective product.
- B. Installer shall warrant for 1 year from the date of completion of work that the work will be free of defects in installation. In the event of any such defect in violation of the warranty, Installer shall have the option to repair or replace any such defective product.

PART 2 - PRODUCTS

2.01 ACCEPTABLE MANUFACTURERS

- A. Strut System and components shall be
 - 1. Atkore UNISTRUT®
16100 South Lathrop Avenue
Harvey, IL 60426
TOLL-FREE / 800-882-5543
Local / (708) 339-1610

2.02 MATERIALS

- A. All channel members shall be fabricated conforming to one of the following ASTM specifications:
 - 1. Plain Carbon Steel: ASTM 1011 SS Grade 33
 - 2. Pre-Galvanized Carbon Steel: A 653 Grade 33
 - 3. Unistrut Defender™: ASTM 1046 SS Grade 33
 - 4. Stainless Steel: A 240 (Type 304)
 - 5. Aluminum: B 221 (Type 6063-T6)
- B. All fittings shall be fabricated conforming to one of the following ASTM specifications:
 - 1. Carbon Steel: All carbon steel fittings shall be fabricated from steel that meets/exceeds the physical requirements of ASTM A1011 SS Grade 33 and conforms to one of the following ASTM specifications:
 - a. ASTM 575
 - b. ASTM 576
 - c. ASTM 36
 - d. ASTM 635
 - e. ASTM1059
 - f. ASTM 1046

2. Stainless Steel:
 - a. ASTM 240 (Type 304 or Type 316)
 - b. ASTM 276 (Type 304 or Type 316)
 3. Aluminum:
 - a. B 209 (Type 1100F or Type 5052-H32)
- C. Any substitutions of product or manufacturer must be approved in writing ten days prior to bid date by the Professional of Record.

2.03 FINISHES

A. FACTORY PAINTED

1. Channel
 - a. Rust inhibiting thermoset acrylic enamel paint applied by electro-deposition after cleaning and phosphating, and thoroughly baked.
2. Fittings
 - a. Polyester powder coat after cleaning and phosphating, and thoroughly baked.
3. Color shall be FHWA Highway Green, Color Tolerance Chart, PR Color No. 4
4. Hardness = 2H
5. Performance
 - a. Salt Spray per ASTM B117
 - (1) Scribed: Exceed 400 hours
 - (2) Unscribed: Exceed 600 hours
 - b. Nominal chalking at 1,000 hours per weatherometer G-23 test
 - c. No checking at 1,000 hours per weatherometer G-23 test

B. ELECTRO-GALVANIZED per ASTM B 633 Type III SC 1

C. PRE-GALVANIZED per ASTM A653

1. Zinc coated by hot-dipped process prior to roll forming at the steel mill
2. Zinc coating thickness shall be G90 (0.75 mil = 0.45 oz./ sq. ft. surface area)

D. HOT-DIPPED GALVANIZED per ASTM A123 or A153

1. Zinc coated after all manufacturing operations are complete
2. Zinc coating thickness shall be G65 (2.6 mils = 1.50 oz./ sq. ft. surface area)

E. UNISTRUT DEFENDER™ per ASTM A1046 and A1059

1. Strut coated per A1046 to a mass of 0.45 oz./ sq. ft. surface area
2. Fittings coated per A1059 to a thickness of 30 microns and/or A1046 to a mass of 0.45 oz./sq. ft. surface area

F. SPECIAL COATING / MATERIAL

(Describe as applicable)

PART 3 - EXECUTION

3.01 EXAMINATION

- A. The installer shall inspect the work area prior to installation. If work area conditions are unsatisfactory, installation shall not proceed until satisfactory corrections are completed.

3.02 INSTALLATION

- A. Installation shall be accomplished by a fully trained manufacturer authorized installer.
- B. Set Strut System components into final position true to line, level and plumb, in accordance with approved drawings.
- C. Anchor material firmly in place and tighten all connections to their recommended torques.

3.03 CLEANUP

- A. Upon completion of this section of work, remove all protective wraps and debris. Repair any damage due to installation of this section of work.

3.04 PROTECTION

- A. During installation, it shall be the responsibility of the installer to protect this work from damage.
- B. Upon completion of this scope of work, it shall become the responsibility of the general contractor to protect this work from damage during the remainder of construction on the project and until substantial completion.

CERTIFICATE OF COMPLIANCE

Certificate Number 20180205-E361025
Report Reference E361025-20130429
Issue Date 2018-FEBRUARY-05

Issued to: UNISTRUT INTERNATIONAL CORP
4205 ELIZABETH ST
WAYNE MI 48184

**This is to certify that
representative samples of**

COMPONENT - MOUNTING SYSTEMS, MOUNTING
DEVICES, CLAMPING DEVICES AND GROUND LUGS
FOR USE WITH PHOTOVOLTAIC MODULES AND
PANELS


See addendum for models.

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety: See addendum for standards.

Additional Information: See the UL Online Certifications Directory at
www.ul.com/database for additional information

Only those products bearing the UL Certification Mark should be considered as being covered by UL's
Certification and Follow-Up Service.

The UL Recognized Component Mark generally consists of the manufacturer's identification and catalog
number, model number or other product designation as specified under "Marking" for the particular
Recognition as published in the appropriate UL Directory. As a supplementary means of identifying products
that have been produced under UL's Component Recognition Program, UL's Recognized Component Mark:
 may be used in conjunction with the required Recognized Marks. The Recognized Component Mark is
required when specified in the UL Directory preceding the recognitions or under "Markings" for the individual
recognitions.

Recognized components are incomplete in certain constructional features or restricted in performance
capabilities and are intended for use as components of complete equipment submitted for investigation rather
than for direct separate installation in the field. The final acceptance of the component is dependent upon its
installation and use in complete equipment submitted to UL LLC.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number 20180205-E361025
Report Reference E361025-20130429
Issue Date 2018-FEBRUARY-05

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Mounting Systems, Mounting Devices, Clamping Devices and Ground Lugs for Use with Photovoltaic Modules and Panels; Photovoltaic Mounting Rail Types:

P1000HS, P1000T, P1000KO, P1000SL, P1000DS and P1000H3 Pre-galvanized
P1000HS, P1000T, P1000KO, P1000SL, P1000DS and P1000H3 Hot Dip Galvanized
P1000HS, P1000T, P1000KO, P1000SL, P1000DS and P1000H3 Stainless Steel (type 304 or type 316)
P1000HS, P1000T Aluminum, anodized, or mill-finish

P1000 DF, P1001 DF, P1000T DF, P1001T DF, P3300 DF, P3301 DF, P3300T DF, P3301T DF, P4100 DF, P4101 DF, P4100T DF, P4101T DF, P5000 DF, P5001 DF, P5000T DF, P5001T DF Unistrut Defender coating (ZAM: Zinc Aluminum Magnesium)

Suffixes indicate mounting hole configurations

Standards for Safety:

UL2703, Mounting systems, mounting devices, clamping/retention devices, and ground lugs for use with flat-plate photovoltaic modules and panels



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



Date: June 29, 2022

Subject: Unistrut Comparison to Power-Strut

From: Unistrut Engineering

Unistrut is made from ASTM A1011 SS (Structural Steel) Grade 33 steel with beam and column loads based on the 2013 Edition of AISI's Cold-Formed Steel Specification.


Unistrut fittings are made from steel conforming to A575, A576, A635, or A36. Except for A36, all steel also conforms to A1011 SS Grade 33 physical requirements. Loads are based on ultimate load testing with an applicable safety factor.

Power-Strut channel and fittings conform to these same requirements. Atkore, Inc. manufactures Unistrut and Power-Strut in the same manner in most cases. The primary difference being the physical stamp on some products which indicates a specific brand's part number.

Sincerely,



Alex Seither
Product Engineer
Atkore, Inc.





Unistrut International
16100 S. Lathrop Ave.
Harvey, IL 60426

Phone: 708-339-1610
800-882-5543
Fax: 708-339-7814

www.unistrut.com

MEMORANDUM

Date: January 19, 2006

Subject: UNISTRUT & MSS SP-58, SP-69 & SP-89

From: Unistrut Engineering

Unistrut actively participates on MSS Committee 403, which is responsible for Standard Practices SP-58, SP-69 & SP-89.

In general, Unistrut products conform to the requirements of MSS SP-58, SP-69 & SP-89 where applicable to the objectives of these standards. Unistrut channel, threaded rod, pipe clamps and beam clamps conform to SP-58, SP-69 & SP-89. By definition, MSS considers continuous concrete inserts (e.g. P3200 Series) devices to which hanger assemblies attach. Therefore, MSS does not have requirements for concrete inserts. However, the material from which Unistrut concrete inserts are made do conform to MSS SP-58, SP-69 & SP-89.



Columbia-MBF



KAF-TECH



UNISTRUT

COPE



UNISTRUT Construction



Date: January 2, 2024

Subject: Unistrut Defender (DF) vs. Hot-Dip Galvanized (HG) Finishes

To Whom It May Concern:

The Unistrut Defender (DF) coating (also known as Atkore Defender™) is a premium finish for outdoor applications and is a drop-in replacement for the Hot-Dip Galvanized (HG) coating. The below table provides a detailed comparison between the two finishes.

Property	Unistrut Hot-Dip Galvanized	Unistrut Defender
Specification(s)	ASTM A1011 SS GR 33, ASTM A123, ASTM A153	ASTM A1046 SS GR 33 ZM90, ASTM A1059
Warranty	1 Year	10 Years
Typical Salt Spray Performance	1,000 hours	3,000 hours
Anticipated Service Life:		
Rural	37 years	100 years
Tropical Marine	29 years	87 years
Temperate Marine	25 years	75 years
Suburban	21 years	63 years
Moderately Industrial	17 years	51 years
Heavy Industrial	9 years	27 years
Self-Healing after Cutting	None Requires coating after cutting channel	Full Self-Healing Does not require coating after cutting channel
Threaded Fasteners	Requires stainless steel or oversized threads, otherwise threads typically bind.	Controlled coating thickness allows easy install of standard fasteners coated in Unistrut Defender.

Additional details about the Unistrut Defender coating can be found on the Atkore website at atkore.com/Atkore-Defender.

If you have any further questions, please feel free to reach out to our Unistrut technical support team at SalesEngineering@atkore.com or (800) 882-5543.

Sincerely,

Milena Solis
Product Manager, Metal Framing N.A.



16100 South Lathrop Avenue
Harvey, IL 60426

Office 708-339-7814

Phone 800-882-5543

Web atkore.com/unistrut

**CERTIFICATE OF COMPLIANCE
BUY AMERICA
BUY AMERICAN**

June 1, 2023

To Whom It May Concern:

This certifies that Unistrut® channel is manufactured in the United States from steel melted and manufactured in the United States. These products comply with the Buy America requirements of 49 U.S.C. 5323(j)(l) and the applicable regulations in 49 CFR part 635.10 and with the Buy American Act of 1933 (FAR 52.225, Sections 9-12). All Unistrut channel finishes are also included as follows:

Plain (PL)

Pregalvanized Zinc (PG)

Hot Dip Galvanized (HG)

Electrocoated Zinc (EG)

Perma-Gold (ZD)

Unistrut Defender (DF)

Copper Clad (CC)

Perma-Green (GR)

Unistrut channel is also available in stainless steel and aluminum and meet both the Buy America and Buy American Acts.

While most Unistrut fittings are also certified as compliant with domestic requirements, please contact Industry Affairs with a specific bill of materials to confirm. Certification letters are also available to include a specific customer or project name upon request.

This certification has been issued for only the products listed above for domestic compliance and is valid for 180 days from date of issue. Alterations to this document by any agency other than Atkore International voids the certification.

Please contact IndustryAffairs@atkore.com if you have any questions.

Atkore Industry Affairs Team

Direct **1.800.882.5543**

Email **Industryaffairs@atkore.com**



Allied Tube & Conduit ▲ AFC Cable Systems ▲ Heritage Plastics ▲ Cii ▲ Unistrut ▲ US Tray
Unistrut Construction ▲ Marco ▲ Calpipe Security ▲ Calbrite ▲ Calbond ▲ Flexicon ▲ Kaf-Tech
Power-Strut ▲ Calconduit ▲ FRE Composites ▲ United Poly Systems ▲ Sasco Strut ▲ Columbia-MBF
Elite Polymer Solutions ▲ Four Star Industries ▲ Eastern Wire + Conduit ▲ ACS/Uni-Fab ▲ Vergokan
Northwest Polymers ▲ Cascade Poly Pipe + Conduit ▲ Razor Ribbon ▲ Queen City Plastics ▲ Cope

Learn more at www.unistrut.us/atkore-defender